

15" x 15", 0.090" FL, Lenticular Array



Stock **#43-027** ☐ In Stock

-

1

+

C\$368.20

ADD TO CART

Qty 1-10
C\$368.20
Qty 11+
C\$320.60
Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
2.29

Substrate: ☐
Acrylic

Coating:
Uncoated

Type:
Lens Array

Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.09
Center Thickness CT (mm): 2.30
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 15 x 15
Dimensions (mm): 381 x 381
Effective Focal Length EFL (inches): 0.09
Effective Size (inches): 15 x 15
Index of Refraction n_d: 1.49
Number of Lenses: 53 per 25.4mm
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Thickness Tolerance (mm): ±0.92

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
