

16.0mm FL, No IR-Cut Filter, f/4, Micro Video Lens



Stock **#83-107** ☐ In Stock

[Similar Products](#)



1



C\$82.60

ADD TO CART

Qty 1-49

C\$82.60

Qty 50+

C\$65.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length (mm):
14.40

Maximum Diameter (mm):
14.0

Maximum Image Circle (mm):
6.00

Horizontal Field of View @ Max Sensor Format:

Resolution, On-Axis:
75 lp/mm @ 20% Contrast

Resolution, 0.7 Field:
65 lp/mm @ 20% Contrast

Resolution, Full Field:
60 lp/mm @ 20% Contrast

Note:
Standard

Type:
M12 Imaging Lens

Focal Length FL (mm):
16.00

Maximum Sensor Format:
1/3"

Working Distance (mm):
400 - ∞

Mount:
M12 x 0.5 (S-Mount)

Aperture (f/#):
f/4

Distortion (%):
-2.5 @ Full Field

IR Cut Filter:
No

Lens Wavelength Range:
VIS

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Reach 224:
[Contains SVHC\(s\)](#)

Certificate of Conformance:
[View](#)