

TECHSPEC® 16.25" Diameter x 80" FL Uncoated, Parabolic Mirror



Stock **#32-725-000** ☐ In Stock

1 **C\$9,790.20**

ADD TO CART

Qty 1-2
C\$9,790.20
Qty 3+
C\$8,321.60
Volume Pricing
Request Quote

Get Product Downloads

Substrate: ☐ [BOROFLOAT®](#)[SUPREMAX®](#)

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 16.25 +0.06/-0
Diameter (mm): 412.80 +1.5/-0
Effective Focal Length EFL (inches): 80.0
Effective Focal Length EFL (mm): 2,032.00
Radius of Curvature (mm): 4,064.00
Aperture (f/#): f/4.9
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Clear Aperture CA (mm): 372
Edge Thickness ET (inches): 3.25
Edge Thickness ET (mm): 82.60
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View