

169 x 194mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock #41-405 ☐ In Stock



1



C\$98.70

ADD TO CART

Qty 1-5

C\$98.70

Qty 6+

C\$79.10

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Flatness (P-V):

4 - 6λ

Substrate: ☐

Float Glass

Surface Quality:

80-50

Dimensions (mm):

169.0 x 194.0 ±0.76
Coating Specification: R _{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 6.00
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 194.00
Width (mm): 169.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant