

16mm Fixed Focal Length Lens



#86-207

Stock **#86-207** [CONTACT US](#)

⊖ 1 ⊕

C\$2,625.00

ADD TO CART

Qty 1+
C\$2,625.00
Volume Pricing
Request Quote

Get Product Downloads

Field of View @ Min Working Distance (mm):
135.00

Iris Option:
Variable

Length (mm):
79.50

Filter Thread:
M40.5 x 0.50

Maximum Diameter (mm):
45.0

Weight (g): 250.00
Maximum Image Circle (mm): 21.60
Horizontal Field of View @ Max Sensor Format: 60.6
Type: Fixed Focal Length Lens
Focal Length FL (mm): 16.00
Maximum Sensor Format: 4/3"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/2 - f/22
Distortion (%): <0.1
Lens Wavelength Range: VIS

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View