

16mm FL Compact Fixed Focal Length Lens



Fixed Focal Length Lenses

Stock **#56-528** ☐ In Stock

[Similar Products](#)



1



C\$595.00

ADD TO CART

Qty 1+

C\$595.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Field of View @ Min Working Distance (mm):
115.00

Iris Option:
Variable

Length (mm):
25.00

Horizontal Field of View, 1/2" Sensor:
22.5°

Filter Thread:

M25.5 x0.50
Maximum Diameter (mm): 30.5
Weight (g): 48.00
Maximum Rear Protrusion (mm): 2.2
Maximum Image Circle (mm): 11.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 16.00
Maximum Sensor Format: 2/3"
Working Distance (mm): 290 - ∞
Mount: C-Mount
Aperture (f/#): f/1.4 - f/16
Lens Wavelength Range: VIS

Regulatory Compliance

Reach 174: Compliant
RoHS: Compliant
Certificate of Conformance: View