

1.8 - 3.0mm FL C-Mount, Manual Iris, Wide Angle Lens



1.8 - 3.0mm FL C-Mount, Manual Iris, Wide Angle Lens, #89-524

Stock **#89-524** [CONTACT US](#)

- 1 +

C\$1,323.00

ADD TO CART

Qty 1+
C\$1,323.00
Volume Pricing
Request Quote

Get Product Downloads

Iris Option: Variable
Length (mm): 45.00
Maximum Diameter (mm): 39.0
Weight (g): 70.00
Horizontal Field of View, 1/3" Sensor: 105 - 77°

Type: Varifocal Lens
Focal Length FL (mm): 1.80 - 3.00
Maximum Sensor Format: 1/2.3"
Working Distance (mm): 500 - ∞
Mount: C-Mount
Aperture (f/#): f/1.8 - Closed
Distortion (%): <1
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View
