

1.8mm FL, No IR-Cut Filter, f/2, Micro Video Lens



Stock **#36-182** ☐ In Stock

1

C\$82.60

ADD TO CART

Qty 1-49

C\$82.60

Qty 50+

C\$65.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length (mm):
15.70

Maximum Diameter (mm):
15.0

Maximum Image Circle (mm):
4.50

Horizontal Field of View @ Max Sensor Format:
122

Resolution, On-Axis: 160 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 80 lp/mm @ 20% Contrast
Resolution, Full Field: 107 lp/mm @ 20% Contrast
Note: Standard
Type: M12 Imaging Lens
Focal Length FL (mm): 1.80
Maximum Sensor Format: 1/4"
Working Distance (mm): 400 - ∞
Mount: M12 x0.5 (S-Mbunt)
Aperture (f/#): f/2
Distortion (%): -76.2
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View