

# 1° Diffusing Angle 25mm Dia., Fused Silica Holographic Diffuser



Holographic UV Diffusers

Stock **#55-848** [CONTACT US](#)



1



C\$640.50

ADD TO CART

Qty 1+

C\$640.50

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Angle Tolerance (°):**  
±0.5

**Diffusing Angle (°):**  
1 (FWHM)

**Clear Aperture CA (mm):**  
21.6 ±0.1

**Diameter (mm):**  
25.00 ±0.1

**Operating Temperature (°C):**  
-40 to +170

Substrate:   
[Fused Silica](#) (Corning 7980)

Transmission (%):  
Typical: 90

Type:  
Holographic Diffuser

Wavelength Range (nm):  
400 - 700

Construction:  
Mounted

Mount Thickness (mm):  
4.7 ±0.1

Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 233:  
[Compliant](#)