

5mW, 635nm Laser Bat Power ZAT



Stock #19-444 **1 In Stock**

⊖ 1 ⊕ C\$400⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	C\$400.40 each
Qty 10+	C\$359.80 each
Need More?	Request Quote



General

Elliptical Dot **Style:**
3R **Laser Class - CDRH:**

Physical & Mechanical Properties

162 **Weight (g):**
124.00 **Length (mm):**

Optical Properties

635.00 **Wavelength (nm):**
Red **Color:**
Up to 2,000mm **Focus Range (mm):**

Electrical

5 **Output Power (mW):**

Hardware & Interface Connectivity

1 AA Battery (Not Included) **Power Requirement:**
Free Space **Output Type:**

Environmental & Durability Factors

IP40 **Environmental Rating:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Bright Red 635nm Wavelength
- Line, Crosshair, or Dot Projection
- Battery Powered Operation with a Fixed Focus
- Sturdy, Metal Housing

Z-Laser ZAT Battery Powered Lasers are ideal for positioning and alignment applications. Their battery powered design provides maneuverability by removing the need for a fixed power supply. IP40 rated, shock proof, and vibration proof with a sturdy, metal housing makes these lasers excellent for harsh environments and repeated use. Z-Laser ZAT Battery Powered Lasers are suitable for use in industrial environments such as Automotive, Paper, Wood, Ceramic, and Metal. Available with 1 or 5mW output powers, the lasers utilize one AA battery (not included) ensuring easy maintenance and an extended lifetime.