

TECHSPEC[®] 1" Dia, 1" FL Enhanced Alum., Spherical Mirror



Stock #43-536 ☐ In Stock

-

1

+

C\$161.00

ADD TO CART

Qty 1-9

C\$161.00

Qty 10+

C\$136.50

Volume Pricing

[Request Quote](#)

Get Product Downloads



Substrate: ☐
BOROFLOAT[®]

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy:

M4
Diameter (inches): 1.0
Diameter (mm): 25.40 +0/-0.3
Diameter Tolerance (inches): +0/-0.01
Effective Focal Length EFL (inches): 1.00
Effective Focal Length EFL (mm): 25.40
Radius of Curvature (mm): 50.80
Aperture (f/#): f/1
Coating: Enhanced Aluminum (450-650nm)
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating Type: Metal
Back Surface: Ground
Edge Thickness ET (inches): 0.25
Edge Thickness ET (mm): 6.35
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant