

TECHSPEC® 1" Dia, 6" FL Uncoated, Spherical Mirror



Stock **#49-595** ☐ In Stock

- 1 + **C\$137.20**

ADD TO CART

Qty 1-9
C\$137.20
Qty 10+
C\$116.90
Volume Pricing
Request Quote

Get Product Downloads



Substrate: ☐ BOROFLOAT®

Focal Length Tolerance (%): ±2

Surface Quality: 60-40

Surface Accuracy:

N4
Diameter (inches): 1.0
Diameter (mm): 25.40 +0/-0.3
Diameter Tolerance (inches): +0/-0.01
Effective Focal Length EFL (inches): 6.00
Effective Focal Length EFL (mm): 152.40
Radius of Curvature (mm): 304.80
Aperture (f/#): f/6
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Edge Thickness ET (inches): 6.35
Edge Thickness ET (mm): 0.25
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View