

1" x 1" (200 lp/inch), Ronchi Ruling



Stock #56-595 ☐ In Stock

-

1

+

C\$239.40

ADD TO CART

Qty 1-4
C\$239.40
Qty 5+
C\$228.06
Volume Pricing
Request Quote

Get Product Downloads

Coating:
Vacuum Deposited Chrome, OD >3.0

Dimensional Tolerance (inches):
±0.02

Substrate:
Float Glass

Optical Density OD (Average):
3.00

Dimensions (inches): 1 x 1
Surface Quality: 60-40
Thickness (mm): 1.50
Type: English
Parallelism (arcmin): ±60
Dimensional Tolerance (mm): ± 0.02
Frequency (lp/inch): 200.00
Line to Line Parallelism (arcsec): ≤2
Parallelism of Pattern to Substrate (°): ±1
Surface Flatness (P-V): 1λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View