

[See all 11 Products in Family](#)

2" Travel, 0.001" Grad., 0.5" Stem Dia. Mic. Drive F-Face



Drive Mechanisms

Stock #33-737 [CONTACT US](#)

- 1 + C\$323⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	C\$323.40 each
Qty 10-24	C\$291.06 each
Need More?	Request Quote

Product Downloads

General

English **Type:**
Mtutoyo **Manufacturer:**

Physical & Mechanical Properties

2 **Travel (inches):**
Graduation (inches):

0.001

12 **Stem Diameter (mm):**

Plain/Flat **Stem/Spindle:**

29 **Stem Length (mm):**

8 **Spindle Diameter (mm):**

34 **Min. Spindle Length (mm):**

21 **Max. Diameter (mm):**

119.5 **Overall Length (mm):**

Hardware & Interface Connectivity

English Micrometer **Type of Drive:**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **REACH 241:**

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
- Compatible with our [Ball Bearing Stages](#)

These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.

Please reference individual product descriptions to see which stages are compatible with each drive mechanism.