

2" x 2" White Advanced Illumination Collimated Backlight

See More by [Advanced Illumination](#)



Advanced Illumination Side-Fired Collimated LED Backlight

Stock **#36-467** ☐ In Stock

-

1

+

C\$868.00

ADD TO CART

Qty 1+

C\$868.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Color:
White

Model Number:
CX0202-WH11C

Operating Temperature (°C):
0 - 60

Dimensions (mm):
115.8 L x 115.8 W x 19.1 T

LED Lifetime (hours):

50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Active Area (inches): 2 x2
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Backlight
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
