

## 20 lp/mm 1" x 3", Opal Glass Ronchi Ruling Slide



Stock **#59-546** 3 In Stock

-

1

+

C\$442<sup>.40</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | C\$442.40 each                |
| Qty 5+         | C\$422.10 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Note:

Pattern Location is Centered

NIST Certification:

No

Physical & Mechanical Properties

Dimensional Tolerance (inches):

±0.100

Length (mm):

25.40

|             |                            |
|-------------|----------------------------|
| 12.7 x25.4  | Pattern Size (mm):         |
| 1.52 ±0.100 | Thickness (mm):            |
| 76.20       | Width (mm):                |
| ±0.001      | Line Width Tolerance (µm): |

Optical Properties

|                         |                               |
|-------------------------|-------------------------------|
| Vacuum Deposited Chrome | Coating:                      |
| 20.00                   | Frequency (lp/mm):            |
| Opal Glass              | Substrate:                    |
| >3.0                    | Optical Density OD (Average): |
| 40-20                   | Surface Quality:              |

Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |
| Compliant | Reach 235:                  |

Product Details

Opal Glass material has been discontinued by the manufacturer and may be available in limited quantities. [Contact us](#) for more information.

- Chrome on Opal
- Test Resolution of Reflective Systems
- High Tolerance