

TECHSPEC® 2.0 OD 50mm Dia UV-NIR ND Filter



UV-NIR Neutral Density Filters

Stock **#88-281** ☐ In Stock

- 1 + **C\$372.40**

ADD TO CART

Qty 1-5

C\$372.40

Qty 6+

C\$334.18

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.2

Optical Density OD (Average):
2.0

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating: Metallic Based ND
Surface Quality: 40-20
Thickness (mm): 5.00 ±0.10
Transmission (%): 1.0
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 190 - 1700
Clear Aperture (%): 80.00
Transmitted Wavefront, P-V: λ/4
Optical Density Tolerance (%): ±10
Parallelism (arcsec): <5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View