

TECHSPEC® 20 x 20mm Protected Silver, λ/4 Mirror



Stock **#49-193** ☐ In Stock

1

C\$94.50

ADD TO CART

Qty 1-5

C\$94.50

Qty 6+

C\$75.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: ☐
[BOROFLOAT®](#)

Back Surface:
Commercial Polish

Surface Quality:

60-40
Dimensions (mm): 20.0 x 20.0
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 2.00 ±0.25
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Length (mm): 20.00
Width (mm): 20.00
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant