

[See all 15 Products in Family](#)

## 200mW, 473nm LC Turnkey Laser Fiber SMA



Low Cost Turnkey Laser & Power Supply (Included)



Stock **#19-505** **2 In Stock**

-

1

+

C\$9,100<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | C\$9,100.00 each              |
| Qty 5+         | C\$8,190.00 each              |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads



| General |                         |
|---------|-------------------------|
| <10     | Warm-Up Time (minutes): |
| Diode   | Type of Laser:          |
| IIIb    | Laser Class - CDRH:     |

|                                   |                                                  |
|-----------------------------------|--------------------------------------------------|
| 10000                             | Mean Time to Failure MTTF (hours):               |
| Physical & Mechanical Properties  |                                                  |
| 142.5 x 60 x 50                   | Dimensions (mm):                                 |
| 27.4                              | Beam Height from Base Plate (mm):                |
| Optical Properties                |                                                  |
| 473.00                            | Wavelength (nm):                                 |
| ±1                                | Wavelength Tolerance (nm):                       |
| Blue                              | Color:                                           |
| 0.22                              | Fiber Numerical Aperture NA (1/e <sup>2</sup> ): |
| Electrical                        |                                                  |
| 200                               | Output Power (mW):                               |
| <2% RMS over 4 hours              | Power Stability (%):                             |
| 1                                 | Modulation Frequency (kHz):                      |
| Hardware & Interface Connectivity |                                                  |
| 88 x 145 x 83                     | Power Supply:                                    |
| 90-264VAC                         | Power Requirement:                               |
| Fiber-Coupled                     | Output Type:                                     |
| SMA                               | Connector:                                       |
| Regulatory Compliance             |                                                  |
| Compliant                         | RoHS 2015:                                       |
| View                              | Certificate of Conformance:                      |
| Compliant                         | Reach 233:                                       |

## Product Details

- Multiple Colors and Wavelengths Available
- Ideal for Microscopy Applications
- TE Cooled

Low Cost Turnkey Lasers offer excellent beam quality and output powers up to 50mW. These lasers feature compact designs for simplified integration and manually adjustable output power through the control box. Each laser features TE cooling and flexible interface allowing for digital or analog modulation, with multiple color and wavelength options available. Low Cost Turnkey Lasers are ideal for research, flow cytometry, and microscope illumination applications.

**Note:** Power supply included. Fiber-coupled lasers include 1m SMA905 coupled fiber.

## Technical Information

