

[See all 17 Products in Family](#)

203.2 x 203.2mm High Intensity 850nm, LED Backlight

See More by [Advanced Illumination](#)



Advanced Illumination High Intensity LED Backlights

Stock **#28-765** [CONTACT US](#)

-

1

+

C\$2,177⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,177.00 each
Need More?	Request Quote

Product Downloads

General	
BL2-0808850IC	Model Number:
50,000	LED Lifetime (hours):
4	Number of Channels:
LED Illuminator	Type of Illumination:
Note:	

Optional Manual Intensity Adjustment #86-887 and #89-555 are Available	
±6 over Illuminated Area (Dependent on Working Distance)	Uniformity (%):
Advanced Illumination	Manufacturer:
Backlight	Geometry:
Constant	Illumination Mode:
Physical & Mechanical Properties	
203.2 H x 203.2 W x 24.1 D	Dimensions (mm):
Optical Properties	
IR	Color:
850	Wavelength (nm):
Hardware & Interface Connectivity	
Flying Leads	Connector:
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	
Environmental & Durability Factors	
0 to 60	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Provides Intense, Even Illumination
- Low Profile Design
- Multiple Active Area Options Available

Advanced Illumination LED Backlights provide intense, even illumination over a range of active areas. Featuring a 50,000-hour product lifetime and a projected light distribution of ±6% over the illuminated area, these lights are ideal for a range of industrial applications. These LED backlights feature a low-profile design with multiple active area options available. Advanced Illumination LED Backlights are offered in white, blue, green, red, and infrared. The backlights are available in 72 H x 72 W x 12 D size, or 123 H x 123 W x 19 D size.

Note: Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately.