

20.4mm Diameter x 25mm FL, MgF₂ Coated, PCX Condenser Lens



Stock **#15-533** ☐ In Stock

[Other Coating Options](#)



1



C\$54.60

ADD TO CART

Qty 1-10

C\$54.60

Qty 11+

C\$49.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
20.40 +0.1/-0.3

Effective Focal Length EFL (mm):
25.00

Numerical Aperture NA:
0.40

Substrate: ☐

Float Glass
Focal Length Tolerance (%): ±7
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Center Thickness CT (mm): 5.30 ±0.2
f/#: 1.23
Bevel: Protective bevel as needed
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant