

20° Diffusing Angle 50mm Dia Mounted



Stock **#54-497** ☐ In Stock

-

1

+

C\$360.50

ADD TO CART

Qty 1-5
C\$360.50
Qty 6+
C\$306.60
Volume Pricing
Request Quote

Get Product Downloads

Angle Tolerance (°):
±2

Diffusing Angle (°):
20 (FWHM)

Clear Aperture CA (mm):
45.7

Diameter (mm):
50.00 ±0.1

Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 2.60
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Construction: Mounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant