


**TECHSPEC®** 20mm 50R/50T Cube Beamsplitter



Stock **#32-504** [CONTACT US](#)

- 1 + **C\$306.60**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| C\$306.60                     |
| Qty 6+                        |
| C\$245.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



**Beam Deviation (arcmin):**  
±3

**Bevel:**  
Protective bevel as needed

**Coating:**  
λ/4 MgF<sub>2</sub> @ 550nm on Faces  
Multilayer Dielectric on Hypotenuse

|                                                                     |
|---------------------------------------------------------------------|
| <b>Construction:</b><br>Cube                                        |
| <b>Dimensions (mm):</b><br>20.0 x 20.0 x 20.0 ±0.10                 |
| <b>Reflection/Transmission Ratio (R/T):</b><br>50/50                |
| <b>Reflection/Transmission Tolerance (%):</b><br>±5                 |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BK7</a> |
| <b>Surface Flatness (P-V):</b><br>λ/4                               |
| <b>Surface Quality:</b><br>60-40                                    |
| <b>Type:</b><br>Standard Beamsplitter                               |
| <b>Wavelength Range (nm):</b><br>400 - 700                          |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 223:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |