

TECHSPEC® 20mm 780nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#47-782** ☐ In Stock

-

1

+

C\$389.20

ADD TO CART

Qty 1-5

C\$389.20

Qty 6+

C\$305.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Clear Aperture (%):
90.00

Coating Specification:

R _{abs} <0.25% @ 780nm
Construction: Cube
Design Wavelength DWL (nm): 780
Dimensions (mm): 20.0 x 20.0 x 20.0 ±0.1
Extinction Ratio: 1000:1
P-Polarization Transmission (%) : >95
S-Polarization Reflection (%) : >99.5
Substrate:  N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 40-20
Type: Linear Polarizer

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View