

TECHSPEC®

20mm Dia., 0.67 Numerical Aperture, Uncoated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#37-424-INK** [CONTACT US](#)

[Other Coating Options](#)



1



C\$413.00

ADD TO CART

Qty 1-5

C\$413.00

Qty 6+

C\$330.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
20.00 ±0.025

Effective Focal Length EFL (mm):
15.00 @ 587.6nm

Numerical Aperture NA:
0.67

Back Focal Length BFL (mm): 8.12
Substrate:  N-SF6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 18.00
Edge Thickness ET (mm): 7.97
Center Thickness CT (mm): 12.42 ±0.10
f/#: 0.75
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 390 - 2500
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View