

TECHSPEC[®] 2.0mm Diameter x 4.0mm Length, N-BK7 Rod Lens



Stock **#54-087** 20+ In Stock

-

1

+

C\$70^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	C\$70.00 each
Qty 6-25	C\$56.00 each
Qty 26-49	C\$53.20 each
Need More?	Request Quote

Product Downloads

General	
Rod Lens	Type:
Physical & Mechanical Properties	
2.00 +0.00/-0.03	Diameter (mm):
4.00	Length (mm):

Length Tolerance (mm):		+0/-0.1
Optical Properties		
N-BK7	Substrate: ☐	
	Coating:	
Uncoated		
Wavelength Range (nm):		
350 - 2200		
Surface Quality:		
40-20		
Regulatory Compliance		
Certificate of Conformance:		
View		

Product Details

- Focuses Collimated Light into a Line
 - Available in Diameters as Small as 1mm
- TECHSPEC® Rod Lenses are polished on the circumference and ground on both ends. Optical performance is similar to a cylinder lens. Collimated light passing through the diameter of the rod lens will be focused into a line. TECHSPEC® Rod Lenses are offered in diameters ranging from 1mm to 10mm.

Technical Information

Rod Lens

