

20X Economical Basic Stereo Microscope



Stock #81-273 **1 In Stock**

- 1 + C\$302.⁴⁰

ADD TO CART

Volume Pricing

Qty 1-4	C\$302.40 each
Qty 5-9	C\$288.40 each
Need More?	Request Quote

Product Downloads

General

None **Type of Illumination:**

40mm total travel; 60mm long rack and pinion **Type of Focusing:**

Magnification with 2X Objective, 10X WF Eyepieces **Note:**

Physical & Mechanical Properties

12.00 **Eye Relief (mm):**

10.00	Field of View (mm):
14.00	Height (inches):
55 - 75	Interpupillary Distance (mm):
139.7 with 80 maximum adjustable	Pole Height (mm):
117 W x 60 H x 190 L	Stage Size (mm):
3.5	Weight (lbs):

Optical Properties

20X	Magnification:
70.0	Working Distance (mm):

Hardware & Interface Connectivity

110 VAC	Power Requirement:
---------	---------------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	------------------------------------

Product Details

- 20X Magnification
- Excellent Eye Relief
- 360° Rotatable Head
- Erect Wide Field Image

Engineered for ease of operation, this quality microscope is a true bargain. Featuring long working distance and excellent depth of field, it accommodates a wide variety of components for inspection. Includes many standard features: adjustable 360° rotatable head, all metal construction, precision rack and pinion focusing with left knob tension adjustment, set-screw locked-in eyepieces, right eyepiece diopter adjustment, 37mm max. object height with adjustable pole height, frosted glass insert, set-screw locked-on stage clips, and dust cover. Optional illumination version (shown) includes 10W, 12V bulbs for incident or transmitted illumination with on/off/on toggle switch and 110V UL listed power supply.