

20X Mitutoyo Plan Apo SL Infinity Corrected Objective

See More by [Mitutoyo](#)



20X Mitutoyo Plan Apo SL Infinity Corrected Objective, #46-398

Stock **#46-398** ☐ In Stock

1

C\$4,562.60

ADD TO CART

Qty 1+

C\$4,562.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Horizontal Field of View, 1/2" Sensor:
0.32mm

Horizontal Field of View, 2/3" Sensor:
0.44mm

Focal Length FL (mm):
10.00

Model Number:

378-810-3
Length excluding Threads (mm): 64.50
Magnification: 20X
Maximum Diameter (mm): 34
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.28
Mounting Threads: M26 x36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 1.0
Depth of Field (µm): 3.50
Field of View, 24 Diameter Field Eyepiece (mm): 1.2
Field of View, 18 Diameter Field Eyepiece (mm): 0.9
Operating Temperature (°C): +5 to +40
Operating Humidity: 20 - 80%
Working Distance (mm): 30.5
Weight (g): 240.00
Wavelength Range (nm): 435 - 655
Style: Infinity Corrected
Manufacturer: Mtutoyo
Parfocal Length (mm): 95
Immersion Liquid: N/A
Exit Pupil Diameter (mm): 5.60

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)