

20X Nikon CFI60 TU Plan Epi ELWD Infinity Corrected Obj

See More by [Nikon](#)



#58-517: 20XNikon CFI60 TU Plan Epi ELWD

Stock **#58-517** ☐ In Stock

-

1

+

C\$3,298.40

ADD TO CART

Qty 1+

C\$3,298.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Field of View (mm):
1.10

Horizontal Field of View, 1/2" Sensor:
0.32mm

Horizontal Field of View, 2/3" Sensor:
0.44mm

Focal Length FL (mm):
10.00

Model Number:

MJE21200
Length excluding Threads (mm): 40.90
Magnification: 20X
Maximum Diameter (mm): 29
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.40
Mounting Threads: M25 x0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 0.7
Depth of Field (µm): 1.72
Field of View, 25 Diameter Field Eyepiece (mm): 1.25
Field of View, 22 Diameter Field Eyepiece (mm): 1.1
Working Distance (mm): 19.00
Weight (g): 90.00
Style: Infinity Corrected
Manufacturer: Nikon
Field Number (mm): 22
Parfocal Length (mm): 60
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View