

2.15" 625nm, LED Darkfield Illuminator

See More by [Advanced Illumination](#)



Stock **#66-791** ☐ In Stock

-

1

+

C\$553.00

ADD TO CART

Qty 1+

C\$553.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Red

Height (mm):
19.0

Inner Diameter (mm):
19.0

Model Number:
RL2115-660-24

Mount: Standard
Operating Temperature (°C): 0 to +65
Outer Diameter (mm): 55.0
Mounting Threads: M3 x2
Wavelength (nm): 625.00
Working Distance (mm): 19 - 25.4
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of LEDs: 15.00
Number of Channels: 1.00
Field Coverage (mm): 6.4 - 12.7
Maximum Trigger Frequency (Hz): 30.00
Type of Illumination: LED Illuminator
Note: Requires a 24V power supply #66-855 . European power supply #35-200 also available.
Manufacturer: Advanced Illumination
Geometry: Ring Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant