

22.2mm Aperture UV/VIS Fiber Optic Collimator, SMA



Fiber Optic Collimator, SMA (SMA adapter inserted)



Stock **#17-567** ☐ In Stock

1

C\$714.00

ADD TO CART

Qty 1-10
C\$714.00
Qty 11+
C\$630.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):

28.58

Substrate: ☐

[Fused Silica](#) (Corning 7980)

Type:

Fiber Collimator
Wavelength Range (nm): 190 - 1250
Aperture Size: 22.2
Compatible Fiber NA: 0.22
Connector: SMA
Fiber Diameter (µm): 800 - 1000
Focal Length FL (mm): 38.00
Housing Material: Stainless Steel
Length (mm): 52.83
Note: Compatible with #17-573 , #17-574 , & #17-575 Refocusing Assemblies
Operating Temperature (°C): -40 to 100

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View