

2.25" x 12.0", 2.0" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock **#46-616** ☐ In Stock

-

1

+

C\$121.80

ADD TO CART

Qty 1-10

C\$121.80

Qty 11+

C\$106.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):

50.80

Substrate: ☐

Acrylic

Coating:

Uncoated

Type:

Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 2.25 x 12.00
Dimensions (mm): 57.15 x 304.8
Effective Focal Length EFL (inches): 2.00
Effective Size (inches): 2.0 x 12.0
Groove Density (grooves/inch): 200.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Transmission (%): 85 (Typical)
Thickness Tolerance (inches): ±0.020

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View