

228nm CWL, 25nm FWHM, 25mm Mounted Diameter



Stock **#68-337** [CONTACT US](#)

[Additional Bandwidths](#)

- 1 +

C\$449.40

ADD TO CART

Qty 1-9
C\$449.40
Qty 10+
C\$403.62
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.25

Angle of Incidence (°):
0

Optical Density OD (Average):
≥4.0

Clear Aperture CA (mm): 21.0
Center Wavelength CWL (nm): 228.00 ±3
Center Wavelength CWL Tolerance (nm): ±3
Full Width-Half Max FWHM (nm): 25.00 ±5
Full Width-Half Max FWHM Tolerance (nm): ±5
Minimum Transmission (%): >20
Operating Temperature (°C): -50 to +50
Coating: Traditional Coated
Surface Quality: 80-50
Type: Bandpass Filter
Typical Applications: Cd Emission Line
Blocking Wavelength Range (nm): 200 - 10000
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 3.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant