

230V, with UK Cord, DC950HK Illuminator

See More by [Dolan-Jenner](#)



230V, with UK Cord, DC950HK Illuminator, #62-006

Stock **#62-006** ☐ In Stock

-

1

+

C\$1,475.60

ADD TO CART

Qty 1+

C\$1,475.60

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
White

Height (inches):
4.5

Length (inches):
9.5

Operating Temperature (°C):
+5 to +40

Type: 150 WEKE Quartz Halogen
Voltage (V): 230
Weight (lbs): 11.5
Width (inches): 7.25
Intensity Control Option: 0.5V DC or 8 bit digital optional
Output Power (Lumens): 1800.00
Construction: Aluminum
Power Supply: ± 0.5% or better regulation
Operating Humidity: 0% to 80% non-condensing
Lamp Lifetime (hours): 200 - 10,000
Ripple (%): 0.4% or better
Type of Illumination: Fiber Optic Illuminator, Incandescent
Manufacturer: Dolan-Jenner
Illumination Mode: Constant

Regulatory Compliance

Reach 174: Compliant
RoHS: Compliant
Certificate of Conformance: View