

## 240mm Length, Fixed Laser Holder



#54-990, #54-991

Stock **#54-991 20+ In Stock**

⊖ 1 ⊕ C\$317<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	C\$317.80 each
Qty 5-25	C\$280.84 each
Qty 26-49	C\$258.72 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Fixed **Type:**  
Cylindrical Tube **Type of Optics:**

### Physical & Mechanical Properties

240.00 **Length (mm):**

660

Weight (g):

Black Anodized Aluminum  
Construction:

Twin Ring Mount Adjustment Screw Pitch (mm):  
0.5

### Threading & Mounting

Size of Compatible Optics (mm):  
20.0 - 55.0

Compatible Post:  
M6 x 1.0

### Regulatory Compliance

RoHS 2015:  
[Exempt](#)

Certificate of Conformance:  
[View](#)

Reach 247:  
[Contains SVHC\(s\)](#)

## Product Details

- Twin Ring Mount Design
- Fixed and Adjustable Versions
- Ideal for He-Ne Lasers

• [Posts](#) and [Post Holders](#) Required for Mounting

Designed for [Helium-Neon Lasers](#), this mount is ideal for any optical tube assembly. [Posts](#) and [Post Holders](#) are required for mounting to a breadboard.

Mounting hole is M6 x 1.0

## Technical Information

