

24mm FL Wide Angle Large Format F-Mount Lenses



Wide Angle Large Format F-Mount Lenses

Stock **#14-262** ☐ In Stock

1

C\$1,589.00

ADD TO CART

Qty 1+
C\$1,589.00
Volume Pricing
Request Quote

Get Product Downloads

Iris Option: Variable
Length (mm): 95.00
Filter Thread: M77 x0.75
Maximum Diameter (mm): 83
Weight (g): 565

Maximum Image Circle (mm): 43.30
Horizontal Field of View, 35mm Sensor: 84.1°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 24.00
Maximum Sensor Format: 35mm
Working Distance (mm): 250 - ∞
Mount: F-Mount
Aperture (f/#): f/1.4 - f/22
Distortion (%): <4
Horizontal Field of View, APS-C Sensor: 61.8°
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View