

TECHSPEC®

2.5 OD 12.5mm Diameter UV-VIS ND Filter



Stock **#48-624** ☐ In Stock

-

1

+

C\$126.00

ADD TO CART

Qty 1-5
C\$126.00
Qty 6+
C\$100.66
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 +0.00/-0.20

Optical Density OD (Average):
2.5

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating:

Metallic Based ND
Surface Quality: 40-20
Thickness (mm): 1.50
Thickness Tolerance (mm): ±0.10
Transmission (%): 0.3
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 250 - 700
Clear Aperture (%): 80.00
Transmitted Wavefront, P-V: λ/4
Optical Density Tolerance (%): ±10
Parallelism (arcsec): <5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant