

25 x 25mm, 25R/75T, AR Coated Plate Beamsplitter



Stock **#13-402** ☐ In Stock

1

C\$77.00

ADD TO CART

Qty 1-9
C\$77.00
Qty 10+
C\$58.80
Volume Pricing
Request Quote

Get Product Downloads



Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: AR N/10 MgF2 @ 550nm

Construction:
Plate

Dimensional Tolerance (mm):
±0.38

Dimensions (mm): 25.00 x25.00
Edges: Cut
Reflection/Transmission Ratio (R/T): 25/75
Substrate: Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 3.00
Type: AR Coated Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant