

SCHOTT KG1, 25mm Sq., 3mm Thick, Colored Glass Heat Absorbing Shortpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#45-647** ☐ In Stock

-

1

+

C\$56.00

ADD TO CART

Qty 1-10

C\$56.00

Qty 11+

C\$50.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Dimensions (mm):
25.0 x 25.0

Density (g/cm³):
2.53

Glass/Filter Number:
[SCHOTT KG1](#)

Substrate: Heat Absorbing Glass
Length (mm): 25.00
Operating Temperature (°C): 300 Maximum
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 60-40
Transformation Temperature (°C): 599
Thickness (mm): 3.00 ±0.38
Type: IR Cut-Off Filter
Width (mm): 25.00
Dimensional Tolerance (mm): ±0.25
Reflection Factor P_d: 0.92
Wavelength Range (nm): 300 - 2700
Bevel: Protective as needed

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View