

25 x 25mm, Rhodium Coated First Surface Mirror



Rhodium Coated First Surface Mirrors

Stock **#15-490** ☐ In Stock

- 1 +

C\$58.10

ADD TO CART

Qty 1-5

C\$58.10

Qty 6+

C\$46.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
80-50

Dimensions (mm): 25.0 x 25.0
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >70% @ 400 - 700nm R _{avg} >90% @ 2000 - 10,000nm
Coating: Rhodium (400-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Edges: Seamed
Thickness (mm): 2.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 400 - 10000
Length (mm): 25.00
Width (mm): 25.00
Coating Abrasion: Severe, per MIL-C-675C Paragraph 3.8.4.1
Coating Adhesion: MIL-PRF-13830B, App B Para. 4.4.6

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant