

TECHSPEC® 25 x 25mm, 1.1mm Thick, Uncoated, Gorilla Glass® Window



Gorilla® Glass Windows



Stock **#12-228** ☐ In Stock

1

C\$40.60

ADD TO CART

Qty 1-5
C\$40.60
Qty 6+
C\$31.15
Volume Pricing
Request Quote

Get Product Downloads



Bevel:
Protective as needed

Chemical Strengthening Cycle (hours):
8

Clear Aperture (%) : 90.00
Clear Aperture CA (mm) : 22.50 x 22.50
Dimensions (mm) : 25.00 x 25.00
Thickness (mm) : 1.10 (nominal)
Coating : Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C) : 7.58 (0 to +300°C)
Density (g/cm³) : 2.39
Edges : Cut and Seamed
Index of Refraction n_d : 1.5
Poisson's Ratio : 0.22
Substrate : Gorilla® Glass
Surface Quality : 80-50
Type : Protective Window
Wavelength Range (nm) : 350 - 2200
Young's Modulus (GPa) : 70
Length (mm) : 25.00
Width (mm) : 25.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 233 : Compliant