

TECHSPEC[®] 25.0mm Dia. x 250.0mm FL, VIS-EXT, Inked, Plano-Convex Lens



Stock #88-733-INK 3-5 DAYS

[Other Coating Options](#)

-

1

+

C\$80.50

ADD TO CART

Qty 1-9

C\$80.50

Qty 10+

C\$72.45

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 ±0.025

Effective Focal Length EFL (mm):
250.00 @587.6nm

Back Focal Length BFL (mm): 248.02
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 2.39
Radius R₁ (mm): 129.20
Clear Aperture CA (mm): 24
f#: 10
Numerical Aperture NA: 0.05
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View