

25.4 x 25.4mm Left-Handed Circular Polarizing Film (CP42HE)



Stock **#88-084** CLEARANCE ☐ In Stock

-

1

+

C\$15.33

ADD TO CART

Qty 1+
C\$15.33

Volume Pricing
Request Quote

Get Product Downloads

Substrate: ☐ Polymer Film CP42HE
Length (mm): 25.40
Operating Temperature (°C): -40 to +80
Dimensions (mm): 25.4 x 25.4
Thickness (mm): 0.27 ±0.04

Transmission (%) : 42.00
Type : Left-Handed Circular Polarizer
Dimensional Tolerance (mm) : +0.0/-0.3
Construction : Polarizing Film
Wavelength Range (nm) : 400 - 700
Polarization Efficiency (%) : >99.90
Heat Resistance (°C x Hours) : 80 x 500
Width (mm) : 25.40
#Sorting : 12.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Contains SVHC(s)