

25.4mm Clear Aperture, 30 Arcsec, Aluminum Retroreflector



Stock **#46-175** ☒ In Stock

1

C\$868.00

ADD TO CART

Qty 1+
C\$868.00

Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcsec): 30.00
Clear Aperture CA (mm): 25.4
Coating: Enhanced Aluminum (450-650nm)
Diameter (mm): 41.30
Exiting Wavefront Accuracy: 3.5λ

Substrate:  BOROFLOAT®
Surface Quality: 80-50
Mounting Threads: (2) ¼-20, M6 x 1.0
Type: Retroreflector
Dimensional Tolerance (mm): ±1.6
Image Orientation: Left-Handed
Ray Deviation (°): 180
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View