

25.4mm Clear Aperture 50R/50T, Pellicle Beamsplitter



Pellicle Beamsplitters

Stock **#39-481** ☐ In Stock

1 **C\$303.80**

ADD TO CART

Qty 1-10

C\$303.80

Qty 11+

C\$258.30

Volume Pricing

[Request Quote](#)

Get Product Downloads



Clear Aperture CA (mm):
25.4

Coating:
Dielectric

Coating Specification:
50/50 @ 632.8nm

Construction: Pellicle
Design Wavelength DWL (nm): 632.8
Diameter (mm): 34.90
Housing: Black Anodized Aluminum
Index of Refraction n_d: 1.5
Mount Thickness (mm): 4.76
Reflection/Transmission Ratio (R/T): 50/50 ±5%
Substrate: ☐ Nitrocellulose
Surface Quality: 40-20
Type: Pellicle Beamsplitter
Mounting Threads: 2-56
Thickness (µm): 2 +0.3/-0.0

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View