

25.4mm Dia f/10 Uncoated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock **#48-175** ☐ In Stock

1

C\$77.00

ADD TO CART

Qty 1-10

C\$77.00

Qty 11+

C\$63.70

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.40 ±0.1

Effective Focal Length EFL (mm):
254.00 @632.8nm

Numerical Aperture NA:

0.05
Back Focal Length BFL (mm): 251.00
Substrate: ☐ PMMA
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 632.8
Coating: Uncoated
Clear Aperture CA (mm): 23.9
Edge Thickness ET (mm): 4.00
Center Thickness CT (mm): 4.58
f##: 10.00
Bevel: Protective bevel as needed
Operating Temperature (°C): 80.00
Radius R (mm): 124.46
Type: Aspheric Lens
Wavelength Range (nm): 400 - 1100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View