

## 25.4mm Dia f/0.75 Uncoated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock **#33-258** ☐ In Stock

-

1

+

C\$84.00

ADD TO CART

Qty 1-10

C\$84.00

Qty 11+

C\$70.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Diameter (mm):**  
25.40 ±0.1

**Effective Focal Length EFL (mm):**  
19.10 @ 632.8nm

**Numerical Aperture NA:**

|                                             |
|---------------------------------------------|
| 0.67                                        |
| Back Focal Length BFL (mm):<br>12.7         |
| Substrate: <input type="checkbox"/><br>PMMA |
| Focal Length Tolerance (%):<br>±1           |
| Aspheric Design Wavelength (nm):<br>632.8   |
| Coating:<br>Uncoated                        |
| Clear Aperture CA (mm):<br>23.9             |
| Edge Thickness ET (mm):<br>4.00             |
| Center Thickness CT (mm):<br>12.22          |
| f##:<br>0.75                                |
| Bevel:<br>Protective bevel as needed        |
| Operating Temperature (°C):<br>80.00        |
| Radius R (mm):<br>99.57                     |
| Type:<br>Aspheric Lens                      |
| Wavelength Range (nm):<br>400 - 1100        |
| Conjugate Distance:<br>Infinite             |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS 2015:<br><a href="#">Compliant</a>             |
| Reach 224:<br><a href="#">Compliant</a>             |
| Certificate of Conformance:<br><a href="#">View</a> |