

**TECHSPEC® 25.4mm Dia. x 3.0mm Thick, 3-12µm AR Coated, Ge Window**



Germanium (Ge) Windows

Stock **#11-868** ☐ In Stock

- 1 + **C\$638.40**

ADD TO CART

Qty 1-10

C\$638.40

Qty 11+

C\$574.70

Volume Pricing

[Request Quote](#)

Get Product Downloads



**Bevel:**  
Protective as needed

**Clear Aperture (%):**  
90.00

**Clear Aperture CA (mm):**  
22.86

|                                                                          |
|--------------------------------------------------------------------------|
| <b>Diameter (mm):</b><br>25.40 +0.0/-0.1                                 |
| <b>Thickness (mm):</b><br>3.00 ±0.1                                      |
| <b>Coating:</b><br>BBAR (3000-12000nm)                                   |
| <b>Coating Specification:</b><br>R <sub>avg</sub> <5.0% @ 3 - 12µm       |
| <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b><br>6.1 |
| <b>Density (g/cm³):</b><br>5.33                                          |
| <b>Edges:</b><br>Fine Ground                                             |
| <b>Index of Refraction n<sub>d</sub>:</b><br>4.002 @ 11µm                |
| <b>Knoop Hardness (kg/mm²):</b><br>780                                   |
| <b>Parallelism (arcmin):</b><br><1                                       |
| <b>Poisson's Ratio:</b><br>0.28                                          |
| <b>Substrate:</b><br>Germanium (Ge)                                      |
| <b>Surface Flatness (P-V):</b><br>λ/10 @ 10.6µm                          |
| <b>Surface Quality:</b><br>60-40                                         |
| <b>Type:</b><br>Protective Window                                        |
| <b>Wavelength Range (nm):</b><br>3000 - 12000                            |
| <b>Young's Modulus (GPa):</b><br>102.7                                   |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |