

25.4mm Diameter Unmounted 0.04-1.0 OD, Circular Variable Neutral Density (ND) Filter



Unmounted Circular Variable Neutral Density (ND) Filters

Stock **#43-759** ☐ In Stock

-

1

+

C\$389.20

ADD TO CART

Qty 1-10
C\$389.20

Qty 11+
C\$350.28

Volume Pricing
Request Quote

Get Product Downloads

Angle of Incidence (°): 0.00
Optical Density OD (Average): 0.04 - 1.0
Substrate: ☐ B270
Inner Diameter (mm):

7.5
Coating: Variable
Outer Diameter (mm): 25.4
Surface Quality: 60-40
Thickness (mm): 1.52
Thickness Tolerance (mm): ±0.25
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Parallelism (arcmin): ±3
Dimensional Tolerance (mm): ±0.10 ID, ±0.20 OD
Optical Density Tolerance (%): ±5
Linearity (%): ±5
Coating Specification: Continuously Variable Inconel from 0 - 270°
Mount: Unmounted

Regulatory Compliance

Reach 181: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View