

TECHSPEC®

25.4mm H x 25.4mm L x 250mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#35-028** ☐ In Stock

1

C\$98.00

ADD TO CART

Qty 1-5

C\$98.00

Qty 6+

C\$78.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Effective Focal Length EFL (mm):
250.00

Substrate:
[N-BK7](#)

f#:
9.84251968503937

Numerical Aperture NA: 0.05
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 248.02
Center Thickness CT (mm): 1.94
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 1.31
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 129.20
Surface Quality: 60-40

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View